


KEMET Part Number: R71MN42204030K
(71MN42204030K)

KEMET
a YAGEO company

R71, Film, Metallized Polypropylene, General Purpose, 2.2 uF, 10%, 420 VDC, 105°C, Lead Spacing = 22.5mm



General Information	
Series:	R71
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	PFC and Pulse
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No
Miscellaneous:	Above 105C DC And AC Voltage Derating Is 4%/C.

Dimensions	
L	26.5mm +0.3/-0.5mm
H	20mm +0.1/-0.5mm
T	11mm +0.2/-0.5mm
S	22.5mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	250

Specifications	
Capacitance:	2.2 uF
Capacitance Tolerance:	10%
Voltage AC:	220 VAC
Voltage DC:	420 VDC
Temperature Range:	-40/+110°C
Rated Temperature:	105°C
Dissipation Factor:	0.1% 25C
Insulation Resistance:	13.6364 GOhms
Max dV/dt:	100 V/us
Resistance:	43.4 mOhms (100kHz)
Ripple Current:	2.45 Amps (100kHz 85C), 220 Amps (Peak)
Inductance:	18 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

KEMET
a YAGEO company