

KEMET Part Number: R75QW41504000J
(75QW41504000J)

R75, Film, Metallized Polypropylene, General Purpose, 1.5 uF, 5%, 1000 VDC, 85°C, Lead Spacing = 37.5mm



General Information	
Series:	R75
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No
Miscellaneous:	Above 85C DC And AC Voltage Derating Is 1.25%/C.

Dimensions	
L	41.5mm +0.3/-0.7mm
H	32mm +0.1/-0.7mm
T	19mm +0.3/-0.7mm
S	37.5mm +/-0.4mm
LL	30mm +5mm
F	1mm +/-0.05mm

Packaging Specifications	
Packaging:	Tray
Packaging Quantity:	96

Specifications	
Capacitance:	1.5 uF
Capacitance Tolerance:	5%
Voltage AC:	250 VAC
Voltage DC:	1000 VDC
Temperature Range:	-55/+105°C
Rated Temperature:	85°C
Dissipation Factor:	0.06% 1kHz
Insulation Resistance:	20 GOhms
Max dV/dt:	150 V/us
Resistance:	5.3 mOhms (100kHz)
Ripple Current:	9.55 Amps (100kHz 85C), 300 Amps (Peak)
Inductance:	20 nH