

KEMET Part Number: R71PR468050H6K
(71PR468050H6K)

R71H, Film, Metallized Polypropylene, Automotive Grade, 6.8 uF, 10%, 630 VDC, 85°C, Lead Spacing = 27.5mm



Dimensions

L	32mm +0.3/-0.7mm
H	30mm +0.1/-0.7mm
T	16mm +0.2/-0.7mm
S	27.5mm +/-0.4mm
LL	25mm +2/-1mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging:	Tray
Packaging Quantity:	144

General Information

Series:	R71H
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	PFC and Pulse
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	AEC-Q200
AEC-Q200:	Yes
Component Weight:	19.9 g
Miscellaneous:	Above 105C DC And AC Voltage Derating Is 4%/C.

Specifications

Capacitance:	6.8 uF
Capacitance Tolerance:	10%
Voltage AC:	220 VAC
Voltage DC:	630 VDC
Temperature Range:	-55/+125°C
Rated Temperature:	85°C
Dissipation Factor:	0.15% 25C
Insulation Resistance:	4.4118 GOhms
Max dV/dt:	80 V/us
Resistance:	9.362 mOhms (100kHz)
Ripple Current:	9.328 Amps (100kHz 85C), 544 Amps (Peak)
Inductance:	18 nH