


R75H, Film, Metallized Polypropylene, Automotive Grade, 15 uF, 5%, 250 VDC, 105°C, Lead Spacing = 37.5mm



General Information

Series:	R75H
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Automotive Grade, Pulse
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	AEC-Q200
AEC-Q200:	Yes
Miscellaneous:	Above 105C DC And AC Voltage Derating Is 1.25%/C.

Dimensions

L	41.5mm +0.3/-0.7mm
H	40mm +0.1/-0.7mm
T	20mm +0.3/-0.7mm
S	37.5mm +/-0.4mm
LL	25mm +2/-1mm
F	1mm +/-0.05mm

Specifications

Capacitance:	15 uF
Capacitance Tolerance:	5%
Voltage AC:	160 VAC
Voltage DC:	250 VDC
Temperature Range:	-55/+125°C
Rated Temperature:	105°C
Dissipation Factor:	0.1% 1kHz
Insulation Resistance:	2 GOhms
Max dV/dt:	40 V/us
Resistance:	0.1 mOhms (100kHz)
Ripple Current:	18.3 Amps (100kHz 90C), 600 Amps (Peak)
Inductance:	20 nH

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	84