

R75H, Film, Metallized Polypropylene, Automotive Grade, 10 uF, 5%, 400 VDC, 105°C, Lead Spacing = 37.5mm



General Information	
Series:	R75H
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Automotive Grade, Pulse
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	AEC-Q200
AEC-Q200:	Yes
Miscellaneous:	Above 105C DC And AC Voltage Derating Is 1.25%/C.

Dimensions	
L	41.5mm +0.3/-0.7mm
H	44mm +0.1/-0.7mm
T	24mm +0.3/-0.7mm
S	37.5mm +/-0.4mm
LL	25mm +2/-1mm
F	1mm +/-0.05mm

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	72

Specifications	
Capacitance:	10 uF
Capacitance Tolerance:	5%
Voltage AC:	220 VAC
Voltage DC:	400 VDC
Temperature Range:	-55/+125°C
Rated Temperature:	105°C
Dissipation Factor:	0.1% 1kHz
Insulation Resistance:	3 GOhms
Max dV/dt:	70 V/us
Resistance:	0.1 mOhms (100kHz)
Ripple Current:	15.59 Amps (100kHz 90C), 700 Amps (Peak)
Inductance:	20 nH