


**KEMET Part Number: R76IN368050H3J**  
(76IN368050H3J)

**KEMET**

a YAGEO company

R76H, Film, Double Metallized Polypropylene, Automotive Grade, 0.68 uF, 5%, 250 VDC, 105°C, Lead Spacing = 22.5mm



#### Dimensions

Dimension	Value
L	26.5mm +0.3/-0.5mm
H	18.5mm +0.1/-0.5mm
T	10mm +0.2/-0.5mm
S	22.5mm +/-0.4mm
LL	25mm +2/-1mm
F	0.8mm +/-0.05mm

#### Packaging Specifications

<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	300

#### General Information

<b>Series:</b>	R76H
<b>Dielectric:</b>	Double Metallized Polypropylene
<b>Style:</b>	Radial
<b>Features:</b>	Automotive Grade, Pulse
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Qualifications:</b>	AEC-Q200
<b>AEC-Q200:</b>	Yes

#### Specifications

<b>Capacitance:</b>	0.68 uF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage AC:</b>	180 VAC
<b>Voltage DC:</b>	250 VDC
<b>Temperature Range:</b>	-55/+125°C
<b>Rated Temperature:</b>	105°C
<b>Dissipation Factor:</b>	0.03% 1kHz, 0.06% 10kHz
<b>Insulation Resistance:</b>	44.11765 GOhms
<b>Max dV/dt:</b>	300 V/us
<b>Resistance:</b>	2.3 mOhms (100kHz)
<b>Ripple Current:</b>	13.55 Amps (100kHz 100C), 204 Amps (Peak)
<b>Inductance:</b>	16 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

**KEMET**

a YAGEO company