


**KEMET Part Number: R76PD0680Z300J**  
(76PD0680Z300J)

R76, Film, Double Metallized Polypropylene, Automotive Grade, 680 pF, 5%, 630 VDC, 85°C, Lead Spacing = 7.5mm



#### Dimensions

Dimension	Value
L	10mm +0.2/-0.5mm
H	8mm +0.1/-0.5mm
T	3mm +0.1/-0.5mm
S	7.5mm +/-0.4mm
LL	17mm +1/-2mm
F	0.5mm +/-0.05mm

#### Packaging Specifications

<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	1750

#### General Information

<b>Series:</b>	R76
<b>Dielectric:</b>	Double Metallized Polypropylene
<b>Style:</b>	Radial
<b>Features:</b>	Automotive Grade, Pulse
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Qualifications:</b>	AEC-Q200
<b>AEC-Q200:</b>	Yes

#### Specifications

<b>Capacitance:</b>	680 pF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage AC:</b>	250 VAC
<b>Voltage DC:</b>	630 VDC
<b>Temperature Range:</b>	-55/+110°C
<b>Rated Temperature:</b>	85°C
<b>Dissipation Factor:</b>	0.03% 1kHz, 0.04% 10kHz, 0.1% 100kHz
<b>Insulation Resistance:</b>	100 GOhms
<b>Max dV/dt:</b>	2800 V/us
<b>Resistance:</b>	936.2 mOhms (100kHz)
<b>Ripple Current:</b>	0.11 Amps (100kHz 85C), 2 Amps (Peak)
<b>Inductance:</b>	8 nH