


KEMET Part Number: R76IW468050H3J
(76IW468050H3J)

R76H, Film, Double Metallized Polypropylene, Automotive Grade, 6.8 uF, 5%, 250 VDC, 105°C, Lead Spacing = 37.5mm



General Information	
Series:	R76H
Dielectric:	Double Metallized Polypropylene
Style:	Radial
Features:	Automotive Grade, Pulse
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	AEC-Q200
AEC-Q200:	Yes

Dimensions	
L	41.5mm +0.3/-0.7mm
H	40mm +0.1/-0.7mm
T	20mm +0.3/-0.7mm
S	37.5mm +/-0.4mm
LL	25mm +2/-1mm
F	1mm +/-0.05mm

Packaging Specifications	
Packaging:	Tray
Packaging Quantity:	84

Specifications	
Capacitance:	6.8 uF
Capacitance Tolerance:	5%
Voltage AC:	180 VAC
Voltage DC:	250 VDC
Temperature Range:	-55/+125°C
Rated Temperature:	105°C
Dissipation Factor:	0.04% 1kHz
Insulation Resistance:	4.41176 GOhms
Max dV/dt:	100 V/us
Resistance:	2.8 mOhms (100kHz)
Ripple Current:	17.09 Amps (100kHz 100C), 680 Amps (Peak)
Inductance:	20 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.