


KEMET Part Number: R76UI110050H4J
(76UI110050H4J)

KEMET
a YAGEO company

R76H, Film, Double Metallized Polypropylene, Automotive Grade, 1000 pF, 5%, 2000 VDC, 105°C, Lead Spacing = 15mm



| General Information | |
|---------------------|---------------------------------|
| Series: | R76H |
| Dielectric: | Double Metallized Polypropylene |
| Style: | Radial |
| Features: | Automotive Grade, Pulse |
| RoHS: | Yes |
| Lead: | Wire Leads |
| Qualifications: | AEC-Q200 |
| AEC-Q200: | Yes |

| Dimensions | |
|------------|------------------|
| L | 18mm +0.3/-0.5mm |
| H | 10mm +0.1/-0.5mm |
| T | 4mm +0.2/-0.5mm |
| S | 15mm +/-0.4mm |
| LL | 25mm +2/-1mm |
| F | 0.8mm +/-0.05mm |

| Packaging Specifications | |
|--------------------------|-----------|
| Packaging: | Bulk, Bag |
| Packaging Quantity: | 1500 |

| Specifications | |
|------------------------|---|
| Capacitance: | 1000 pF |
| Capacitance Tolerance: | 5% |
| Voltage AC: | 700 VAC |
| Voltage DC: | 2000 VDC |
| Temperature Range: | -55/+125°C |
| Rated Temperature: | 105°C |
| Dissipation Factor: | 0.03% 1kHz, 0.04% 10kHz, 0.1% 100kHz |
| Insulation Resistance: | 100 GOhms |
| Max dV/dt: | 9500 V/us |
| Resistance: | 636.6 mOhms (100kHz) |
| Ripple Current: | 0.44 Amps (100kHz 100C), 10 Amps (Peak) |
| Inductance: | 10 nH |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

KEMET
a YAGEO company