


KEMET Part Number: R76UR24704030J
(76UR24704030J)

R76, Film, Double Metallized Polypropylene, General Purpose, 0.047 uF, 5%, 2000 VDC, 85°C, Lead Spacing = 27.5mm



Dimensions

L	32mm +0.3/-0.7mm
H	20mm +0.1/-0.7mm
T	11mm +0.2/-0.7mm
S	27.5mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging:	Tray
Packaging Quantity:	336

General Information

Series:	R76
Dielectric:	Double Metallized Polypropylene
Style:	Radial
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No

Specifications

Capacitance:	0.047 uF
Capacitance Tolerance:	5%
Voltage AC:	700 VAC
Voltage DC:	2000 VDC
Temperature Range:	-55/+110°C
Rated Temperature:	85°C
Dissipation Factor:	0.03% 1kHz, 0.04% 10kHz, 0.1% 100kHz
Insulation Resistance:	100 GOhms
Max dV/dt:	2500 V/us
Resistance:	33.9 mOhms (100kHz)
Ripple Current:	4.34 Amps (100kHz 85C), 108 Amps (Peak)
Inductance:	18 nH