


KEMET Part Number: R79GC3220Z340J
(79GC3220Z340J)

KEMET

a YAGEO company

R79, Film, Metallized Polypropylene, General Purpose, 0.22 uF, 5%, 160 VDC, 85°C, Lead Spacing = 5mm



General Information

Series:	R79
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Pulse
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No
Component Weight:	1.08 g
Miscellaneous:	Above 85C DC And AC Voltage Derating Is 1.25%/C.

Dimensions

L	7.2mm +0.3/-0.5mm
H	13mm +0.1/-0.5mm
T	7.2mm +0.1/-0.5mm
S	5mm +/-0.4mm
LL	17mm +1/-2mm
F	0.5mm +/-0.05mm

Specifications

Capacitance:	0.22 uF
Capacitance Tolerance:	5%
Voltage AC:	70 VAC
Voltage DC:	160 VDC
Temperature Range:	-55/+105°C
Rated Temperature:	85°C
Dissipation Factor:	0.06% 1kHz, 0.1% 10kHz
Insulation Resistance:	100 GOhms
Max dV/dt:	100 V/us
Inductance:	6 nH

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	750

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

KEMET

a YAGEO company