


KEMET, VA, Varistors, Automotive, 34 V, 30 VAC, 47 V, 50 V, 77 V, 5 A, 800 A, 3.8 J, 6 J, 15 mW



General Information	
Supplier:	KEMET
Series:	VA
Type:	Varistors
Style:	SMD Chip
Description:	SMD 125C Multilayer Chip Varistor, 24V Power Supply
Features:	Automotive
Termination:	Nickel Tin
RoHS:	Yes
AEC-Q200:	Yes

Dimensions	
Chip Size	1812
L	4.7mm +/-0.4mm
W	3.2mm +/-0.3mm
T	1.3mm MAX
B	0.5mm +/-0.25mm

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	1000

Specifications	
Voltage DC:	34 VDC (25C)
Voltage AC:	30 VAC
Temperature Range:	-55/+125°C
Storage Temperature Range:	-55/+150°C
Varistor Voltage:	47 VDC at 1 mA
Jump Start Voltage:	50 VDC (5 min)
Clamping Voltage:	77 V
Clamping Current:	5 A (8/20 us MAX)
Surge Current:	800 A (8/20 us MAX)
Energy:	3.8 J (10/1000 us MAX)
Load Dump:	6 J
Capacitance:	2.2 nF (1kHz)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.